FUTEK MODEL LCM300

Tension and Compression Load Cell (Miniature/Inline Threaded)

Drawing Number: FI1059-B	
INCH [mm]	R.O.= Rated Output

WIRING CODE (WC1)			
+Excitation	-Excitation	+Signal	-Signal
RED	BLACK	GREEN	WHITE
Shield			
FLOATING			



ITEM #	CAPACITIES lb	N
FSH02699	50	223
FSH02700	100	445
FSH02701	250	1112
FSH02702	500	2224
FSH02703	1000	4448

SPECIFICATIONS:

RATED OUTPUT	*2 mV/V nom.*
SAFE OVERLOAD	*150% of R.O.*
ZERO BALANCE	*±3% of R.O.*
EXCITATION (VDC OR VAC)	*15 MAX*
BRIDGE RESISTANCE	*700 Ω nom.*
NONLINEARITY	*±0.25% of R.O.*
HYSTERESIS	*±0.25% of R.O.*
NONREPEATABILITY	*±0.1% of R.O.*
TEMP. SHIFT ZERO	*±0.005% of R.O./°F [0.01% of R.O./°C]*
TEMP. SHIFT SPAN	*±0.02% of LOAD/°F [0.036% of LOAD/°C]*
COMPENSATED TEMP.	*60 to 160°F [15 to 72°C]*
OPERATING TEMP.	*-45 to 200°F [-42 to 93°C]*
WEIGHT	*2oz. [57g]*
MATERIAL (FLEXURE)	*17-4PH S.S.*
DEFLECTION	*0.001 to 0.002 [0.03 to 0.05] nom.*

CABLE: #28 AWG, 4 Conductor, Braided Shielded PVC Cable 10 ft [3 m] Long

ACCESSORIES AND RELATED INSTRUMENTS AVAILABLE

CALIBRATION (STD)	*5 pt TENSION; 100 K Ω SHUNT CAL. VALUE*
CALIBRATION (AVAILABLE)	*COMPRESSION*
CALIBRATION TEST EXCITATION	*10 VDC*

ITEM #'S IN THE TABLE HAVE REPLACED: 50lb-FSH00666, 100lb-FSH00667, 250lb-FSH00668, 500lb-FSH00669, 1Klb-FSH00670

FUTEK
ADVANCED SENSOR TECHNOLOGY, INC.

This drawing is submitted solely for the information and exclusive use of the original addressee. It is not to be divulged in whole or in part, by any firm or individual without written permission from FUTEK

10 THOMAS
IRVINE, CA 92618 USA
+1 (949) 465-0900

INTERNET:
http://www.futek.com