



FUTEK MODEL ZCC992

8 Pin Binder w/ Cable Assembly For FUTEK Model IHH500

DRAWING NUMBER: F11359

INCH [mm] | R.O.= Rated Output




SPECIFICATIONS:

CABLE: 30 AWG, 10 CONDUCTOR BRAIDED SHIELDED POLYURETHANE
DIAMETER: 0.174 [4.4]
CABLE MINIMUM BEND RADIUS: 1.74 [44.2]

TEMPERATURE: -40° TO 176°F [-40° TO 80°C]
IP RATING: IP67*

*WHEN MATED WITH CONNECTOR



Pin	Color	Description
1	WHITE	ANALOG CURRENT OUTPUT
2	RED	ANALOG VOLTAGE OUTPUT RETURN
3	ORANGE	(+) SOLID STATE RELAY 1
4	GREEN	ANALOG VOLTAGE OUTPUT
5	YELLOW	(+) SOLID STATE RELAY 2
6	BLACK	ANALOG CURRENT OUTPUT RETURN
7	BLUE	(-) SOLID STATE RELAY 1
8	GRAY	(-) SOLID STATE RELAY 2