





FUTEK MODEL IAC180
ITEM # FSH03088

POWER SUPPLY KIT FOR CSG110 AMPLIFIER

Drawing Number: FI1301-C


INCH [mm]

INTERCHANGEABLE PLUGS



POWER SUPPLY (AFTER AUG. 2011)
 90-264 VAC to 15 VDC, 18 W

POWER SUPPLY (UNTIL AUG. 2011)
 120 VAC to 12 VDC, 1000 mA



DB9 FEMALE CONNECTOR

SCREW TERMINAL BLOCKS

6.5 FT POWER CABLE

OUTPUT CABLE: 5 FT
 #28 AWG 6 COND. BRAIDED
 SHIELDED CLEAR POLYURETHANE

PIN #	WIRING CODE	CABLE COLOR CODE
9	12 VDC	POWER CABLE W/ WHITE STRIPE
8	SIGNAL OUT (VOLTAGE)	GREEN
7	RETURN (VOLTAGE)	ORANGE
6	GROUND	POWER CABLE W/O WHITE STRIPE
3	N/A	SHIELD
2	RETURN (CURRENT)	BLUE
1	SIGNAL OUT (CURRENT)	WHITE


FEATURES:

- 120 VAC Wall Socket Power Supply Converter to 15 VDC Included

SPECIFICATIONS:

- Max Current: 1 Amp
- Operating Temperature: 32°F (0°C) to 104°F (40°C)
- Storage Temperature: -40°F (-40°C) to 185°F (85°C)
- 95% Relative Humidity Non-Condensing

DB9 FEMALE PIN OUTS



DB9 PIN CALLOUTS

