

FUTEK MODEL IHH300 (D531)

STOCK NUMBER: SEE BELOW


HAND HELD PORTABLE DIGITAL DISPLAY FOR USE W/ ANY STRAIN GAGED SENSOR (PREVIOUSLY D530 SERIES)

Drawing Number: FI1022

INCH [mm]

FEATURES:

- 8000 Samples per second
- Maximum reading 9999 with floating decimal point
- Input range 1-4 mV/V
- Powered by 9 volt rechargeable battery (supplied)
- Battery life of up to 20 hrs (Depending on use and battery condition)
- Supplied with charging adapter (110V input)
- 5 Selectable filter settings 170, 250, 500, 1500, 3600 Hz
- RS232C (Printer Output), Supplied with cable and connector (4800 Baud, No parity, 8 Data, 1 Stop Bit)
- Operation Modes- Track, Peak/Valley, First Peak/Valley Hold
- Display can store 15 different custom sensor calibrations
- Stores up to 1000 Data points
- Includes Data number, indicated value and units
- Limit Settings- User selectable % of target or high low values
- Buzzer and 3 LED warnings- Yellow (under), Green (within), Red (over)
- Weight: 8 oz [0.23 Kg]



ENVIRONMENT:

- Operating Temperature: 32 to 105°F [0 to 41°C]
- Storage Temperature: 32 to 105°F [0 to 41°C]
- Relative Humidity: 0 / 95° non-condensing

STOCK #S

- STK# FSH01439- Torque Display (ft-lb, in-lb, in-oz, N-m, cN-m, Kgf-m)
- STK# FSH01906- Load Display (lb,N,Kn,Kg, g)

