








FEATURES

- Compatible in load washer applications
- Offered in a variety of capacities and inner diameters
- Low power consumption
- Fast response (μ s) and low deflection
- Environmental Protection, IP67 Rated
- Water Resistant and Outdoor Rated
- Quick Disconnect Cable

-  Non-loading surface, do not contact
-  Active End
-  Fixed End

+ Output (compression)



SPECIFICATIONS

PERFORMANCE

Nonlinearity	$\pm 0.5\%$ of RO
Hysteresis	$\pm 0.5\%$ of RO $\pm 1\%$ of RO (50,000 lbs)
Nonrepeatability	$\pm 0.5\%$ of RO

ELECTRICAL

Rated Output (RO)	2 mV/V nom
Excitation (VDC or VAC)	18 max
Bridge Resistance	700 Ohm nom
Insulation Resistance	≥ 500 MOhm @ 50 VDC
Connection	4 Position Micro Receptacle
Wiring Code	CC19

MECHANICAL

Capacities	Refer to online store for available capacities (up to 50,000 lbs) and ID Size Combinations.
Weight (approximate)	26 oz [737 g]
Safe Overload	150% of RO
Deflection	0.002 in [0.05 mm] nom
Material	17-4 PH stainless-steel
IP Rating	IP67

TEMPERATURE

Operating Temperature	-60 to 200°F (-50 to 93°C)
Compensated Temperature	60 to 160°F (15 to 72°C)
Temperature Shift Zero	$\pm 0.005\%$ of RO/°F (0.01% of RO/°C)
Temperature Shift Span	$\pm 0.005\%$ of Load/°F (0.01% of Load/°C)

CALIBRATION


Calibration Test Excitation	10 VDC
Calibration (standard)	5-pt Compression
Shunt Calibration Value	100 kOhm

CONFORMITY

RoHS	EU 2015/863
CE	EN55011; EN61326-1

DIMENSIONS inches [mm]

TOLERANCE:
 .X ± 0.1" [2.5]
 .XX ± 0.01" [0.25]
 .XXX ± 0.005" [0.127]



FUTEK 4 PIN MICRO CIRCULAR (CC19)

1	+ EXCITATION	Red
2	- EXCITATION	Black
3	- SIGNAL	White
4	+ SIGNAL	Green



Note: While torquing bolts, high tension forces will occur during installation, which could result in overloading the sensor. FUTEK recommends connecting the sensor to a system in order to monitor the applied forces. FUTEK is not liable or responsible for the mishandling of the sensor during installation.

INNER DIAMETER (Actual)

ID	Dimension ^{+0.01} _{-0.00} [^{+0.25} _{-0.00}]
3/8	0.384 [9.75]
1/2	0.509 [12.93]
9/16	0.572 [14.53]
5/8	0.634 [16.10]
3/4	0.769 [19.53]
7/8	0.894 [22.71]
1	1.019 [25.88]
1 1/4	1.269 [32.23]

Drawing Number: F11552

FUTEK reserves the right to modify its design and specifications without notice. Please visit www.futek.com/salesterms for complete terms and conditions.

10 Thomas, Irvine, CA 92618 USA
 Tel: (949) 465-0900

www.futek.com



RoHS



U.S. Manufacturer