





### LEMO 4-PIN (CC4)


PIN	COLOR	DESCRIPTION
1	Red	+ Excitation
2	Green	+ Signal
3	White	- Signal
4	Black	- Excitation



Align with key  
Front View




### DIMENSIONS inches [mm]



### FEATURES

- Easily inserts and detaches from sensor
- 85% Braided Shield coverage for optimal EMI protection
- Latching feature for cable security
- Keyed to ensure proper mate and pin alignment
- Flexible PVC Cable with molded strain relief



### VARIATIONS

ITEM #	LENGTH [FT]	CABLE/CONNECTORS	MATES TO	TEMPERATURE	SPECIFICATIONS
FSH01790	15	ZCC940 to Cable Assembly	Flying Leads (Bare Wires)	-40 to 221°F (-40 to 105°C)	4 Pin Lemo to Cable Assembly, IP50, 28 AWG, 4 Conductor Braided Shielded Clear PVC, RoHS Compliant
FSH01785	30				
FSH02114	100				
FSH04471	15	ZCC940 to Binder Male Plug 99 5129 00 12 with TEDS (IEEE1451.4)	IHH500 with TEDS IEEE1451.4	-22 to 203°F (-30 to 95°C)	
FSH04472	15	ZCC940 to Binder Male Plug 99 5129 00 12	IHH500/USB520		
FSH04473	15	ZCC940 to 12 Pin Hirose	USB215/USB220	-40 to 158°F (-40 to 70°C)	

Drawing Number: FI1538

FUTEK reserves the right to modify its design and specifications without notice. Please visit <http://www.futek.com/salesterms> for complete terms and conditions.

10 Thomas, Irvine, CA 92618 USA  
Tel: (949) 465-0900

[www.futek.com](http://www.futek.com)



U.S. Manufacturer