


FUTEK MODEL ZCC994
ITEM #: FSH03669

12 Pin Binder To 8 & 6 Pin Screw Terminal Cable Assembly
FOR FUTEK MODEL IPM650

Drawing Number: FI1343


INCH [mm]



FRONT VIEW

PIN	WIRING CODE (CABLE 1)
A	+EXCITATION (RED)
B	+SIGNAL (GREEN)
C	-EXCITATION (BLACK)
D	-SIGNAL (WHITE)
E	TEDS (ORANGE)
G	GROUND (BLUE)

PIN	WIRING CODE (CABLE 2)
F	24V OUT (ORANGE)
G	GROUND (BLUE & BLACK)
H	5V OUT (RED)
J	-VOLTAGE INPUT (WHITE)
K	+VOLTAGE INPUT (GREEN)



MOUNTING CUTOUT	CABLE	SPECIFICATIONS
<p>PANEL THICKNESS: MIN. 0.039 [1.0] MAX. 0.157 [4.0]</p>	<p>28 AWG, 6 CONDUCTOR BRAIDED SHIELDED POLYURETHANE</p> <p>DIAMETER: 0.165 [4.2]</p> <p>CABLE MINIMUM BEND RADIUS: 1.65 [41.9]</p>	<p>TEMP: -40° to 176°F [-40° to 80°C]</p> <p>IP RATING IP67*</p>

* When mated with connector