




VARIATIONS			
ITEM #	LENGTH [FT]	CABLE	SPECIFICATIONS
FSH03678	5	28 AWG, 4 conductor braided shielded clear PVC Diameter: 0.115 in [2.9 mm]	Temperature: -40 to 176°F -40 to 80°C IP RATING: IP50
FSH03679	10		
FSH03680	15		
FSH03681	20		
FSH03682	30		
FSH03683	50	Cable Minimum Bend Radius: 1.15 in [29.2 mm]	IP RATING: IP50
FSH03684	100		
FSH03685	200		

FEATURES

- Simplifies integration with USB220 and USB320
- High stranded, braided shielded, flexible PVC cable
- 12-pin cable assembly

WIRING CODE (WC1)		
COLOR	PIN #	CODE
GREEN	1	+ SIGNAL
WHITE	2	- SIGNAL
RED	11	+ EXCITATION
BLACK	12	- EXCITATION / SHIELD

DIMENSIONS inches [mm]



Drawing Number: FI1346-B

FUTEK reserves the right to modify its design and specifications without notice. Please visit <http://www.futek.com/salesterms> for complete terms and conditions.

10 Thomas, Irvine, CA 92618 USA

Tel: (949) 465-0900

Fax: (949) 465-0905

www.futek.com



U.S. Manufacturer