


FUTEK MODEL APA300

IPM650 Power Supply, AC/DC wall mount
adapter 15V 18W

DRAWING NUMBER: F11512

INCH [mm] | R.O.= Rated Output



Europe 2 Prong

United Kingdom 3 Prong

Australia 2 Prong

AC Plug Configuration	
U.S. 2-prong	US
United Kingdom 3-prong	UK
Europe 2-prong	EU
Australia 2-prong	AU

FEATURES

- Interchangeable AC Plug Configurations
- Overload and short circuit protection
- Input Voltage: 100 to 240VAC
- Output Voltage: 15V
- Maximum Power: 18W
- Maximum Current Output: 1.2A
- IP22 Rated Enclosure
- RoHS Compliant
- Meets UL/EN/IEC60601-1-2, 4th ed. for EMC
- CE Certified

ENVIRONMENT

- Operating Temperature: -4° F to +104° F [-20° C to +40° C], up to +158° F [+70° C] with applicable power derating.
- Storage Temperature: -40° F to +185° F [-40° C TO +85° C]