


DIMENSIONS inches [mm]



FEATURES

- Interchangeable AC plug configurations
- US and EU interchangeable AC plugs can be inserted in multiple orientations (straight or 90°) **indicated with an asterisk (*)**
- Overload and short circuit protection
- Input voltage: 90-264 VAC
- Output voltage: 15 VDC
- Maximum current output: 1.2 A
- Maximum power output: 18 W
- CE certified
- RoHS compliant
- UL listed


ENVIRONMENT

- Operating temperature: 32°F to 104°F [0°C to 40°C]
- Storage temperature: -40°F to 185°F [-40°C to 85°C]

COLOR CODE

BLACK	POWER
BLACK WITH WHITE STRIPE	GROUND

AC PLUG CONFIGURATION



Drawing Number: FI1393

FUTEK reserves the right to modify its design and specifications without notice. Please visit <http://www.futek.com/salesterms> for complete terms and conditions.

10 Thomas, Irvine, CA 92618 USA

Tel: (949) 465-0900

Fax: (949) 465-0905

www.futek.com



RoHS



U.S. Manufacturer