




AC PLUG CONFIGURATION

US 2-PRONG	US
UNITED KINGDOM 3-PRONG	UK
EUROPE 2-PRONG	EU
AUSTRALIA 2-PRONG	AU

DIMENSIONS inches [mm]



FEATURES

- Interchangeable AC Plug Configurations
- Overload and short circuit protection
- Input Voltage: 100 to 240VAC
- Output Voltage: 15V
- Maximum Power: 18W
- Maximum Current Output: 1.2A
- IP22 Rated Enclosure
- RoHS Compliant
- Meets UL/EN/IEC60601-1-2, 4th ed. for EMC
- CE Certified

ENVIRONMENT

- Operating Temperature: -4°F to +104°F [-20°C to +40°C], up to +158°F [+70°C] with applicable power derating.
- Storage Temperature: -40°F to +185°F [-40°C TO +85°C]

Drawing Number: FI1512-A

FUTEK reserves the right to modify its design and specifications without notice. Please visit <http://www.futek.com/salesterms> for complete terms and conditions.

10 Thomas, Irvine, CA 92618 USA

Tel: (949) 465-0900
Fax: (949) 465-0905

www.futek.com



RoHS



U.S. Manufacturer