



SPECIFICATIONS


MATERIAL

Shell	Brass
Inserts & Insulators	PEEK
Contacts	Gold plate


APPLICABLE STANDARD

Working Voltage	400 V rms @ sea level
Dielectric Withstanding Voltage	1000 V rms @ sea level
Contact Current	1 A max
Operating Temperature	-60 to 500°F (-51 to 260°C)
Contact Resistance	4.0 mOhms max @ 1 A
Mating Cycles	5000
Max Wire Gauge	28 AWG

DIMENSIONS inches [mm]



**4 PIN MICROTECH
RECEPTACLE DR-4S-4
/CMR-O2-D-04P**



**4 PIN MICROTECH
RECEPTACLE**

**MAX CABLE JACKET DIAMETER-
0.124 [3.15]**

MICROTECH 4-PIN

PIN	WIRING CODE
A	+ Excitation
B	- Excitation
C	+ Signal
D	- Signal

Drawing Number: F11418-B

FUTEK reserves the right to modify its design and specifications without notice. Please visit <http://www.futek.com/salesterms> for complete terms and conditions.

10 Thomas, Irvine, CA 92618 USA

Tel: (949) 465-0900

Fax: (949) 465-0905

www.futek.com



U.S. Manufacturer