






## FEATURES

- High accuracy
- Overload protection
- For use in both tension and compression
- Integrated connector, detachable cable available
- Notable non-repeatability

**IMPORTANT NOTE: DO NOT ROTATE THE LOADING ROD AS IT WILL CAUSE DAMAGE TO THE SENSOR**



Fixed end

## SPECIFICATIONS

### PERFORMANCE

Nonlinearity	±0.05% of RO
Hysteresis	±0.05% of RO
Nonrepeatability	±0.05% of RO
Creep	±0.05% of Load

### ELECTRICAL

Rated Output (RO)	2 mV/V nom
Excitation (VDC or VAC)	18 max
Bridge Resistance	1000 Ohm nom
Insulation Resistance	≥500 Mohm @ 50 VDC
Connection	4 Pin LEMO Receptacle
Connector Code	CC4

### MECHANICAL

Weight (approximate)	5 oz [140 g]
Safe Overload	See chart on next page
Material	Aluminum, Red Anodized (Housing)
IP Rating	IP40

### TEMPERATURE

Operating Temperature	-60 to 200°F [-50 to 93°C]
Compensated Temperature	60 to 160°F [15 to 71°C]
Temperature Shift Zero	±0.005% of RO/°F [0.01% of RO/°C]
Temperature Shift Span	±0.005% of Load/°F [0.01% of Load/°C]

### CALIBRATION


Calibration Test Excitation	10 VDC
Calibration (standard)	5-pt compression
Calibration (available)	Tension and Compression
Shunt Calibration Value	150 kOhm

### CONFORMITY

RoHS	EU 2015/863
CE	EN55011; EN61326-1

**DIMENSIONS** inches [mm]

TOLERANCE:  
 .X ± 0.1" [2.5 mm]  
 .XX ± 0.01" [0.25 mm]  
 .XXX ± 0.005" [0.127 mm]




**CAPACITIES**

ITEM #	lb	N	Safe Overload (lb)	Deflection (in)	Natural Frequency (Hz)
FSH04036	0.25	1.1	50	0.0078	120
FSH04037	0.50	2.2	50	0.0075	170
FSH04038	1	4.5	50	0.0067	260
FSH04039	2.2	9.8	250	0.0084	210
FSH04040	5	22.2	250	0.0065	350
FSH04041	10	44.5	250	0.0059	520
FSH04042	25	111	250	0.0052	860
FSH04043	50	222	250	0.0050	1250
FSH04044	100	445	250	0.0050	1760

**LEMO 4-PIN (CC4)**

PIN	COLOR	DESCRIPTION
1	Red	+ Excitation
2	Green	+ Signal
3	White	- Signal
4	Black	- Excitation



Drawing Number: F11435-C

FUTEK reserves the right to modify its design and specifications without notice.  
 Please visit [www.futek.com/salesterms](http://www.futek.com/salesterms) for complete terms and conditions.

10 Thomas, Irvine, CA 92618 USA  
 Tel: (949) 465-0900

[www.futek.com](http://www.futek.com)



RoHS



U.S. Manufacturer