


Extraneous Load Factors



Equation: $\sigma_{max} \geq (A)Fx + (B)Fy + (C)Fz + (D)Mx + (E)My + (F)Mz$

Material: 17-4 P.H. Stainless Steel

Model #	Capacity (lb)	A	B	C	D	E	F
LCM200	250	1240	6000	116	9400	1500	3200
	500	1240	6000	116	9400	1500	3200
	1,000	680	4900	58	4200	1160	2080

σ_{max} **Table**

Material	Static Load (=60% Y.S.)	Fatigue (Non Reversing Loads)	Fatigue (Full Reversing Loads)
17-4PH S.S	87,000	78,000	62,000*

*Value is 75% of Fatigue Strength based on 10-20 x 10⁶ cycles and allow for factors that influence Fatigue such as surface finish, stress concentrations, corrosion, temperature and other variables for the production of the transducer, for infinite Fatigue Life (100 x 10⁶) use 75% of values shown.

Deflection & Natural Frequency

Model #	Capacity (lb)	Deflection (in.)	Natural Frequency (Hz)	β
LCM200	250	0.0002	31000	0.016
	500	0.0003	33000	0.016
	1,000	0.0005	27000	0.017

Natural Frequency & Frequency Response Equation's:

$$\text{Natural Frequency (FN)} = 3.13 \sqrt{\frac{1}{\frac{\beta}{Capacity} \cdot Deflection}} \text{ (Hz)}$$

$$\text{Frequency Response with load (FR)} = 3.13 \sqrt{\frac{1}{\frac{\beta + AppliedLoad}{Capacity} \cdot Deflection}} \text{ (Hz)}$$

*Where β values are obtained by Futek Engineers

This documentation was generated and completed to the best ability of FUTEK's Engineering Team using FEA Analysis, Empirical data and Multiple Testing Simulations. The information and recommendations on this document are presented in good faith and believed to be correct however, FUTEK Advanced Sensor Technology makes no representations or warranties as to the completeness or accuracy of the information.