

MODEL USB220 High Resolution USB Output Module



FEATURES

- USB 2.0 Communication Link •
- USB Bus-Powered (5V) •
- Integrated Shunt Cal
- Streaming ASCII Output •
- Input/Output Short Circuit Protection •

SPECIFICATIONS	
GENERAL	
Item Number	FSH03456
Sampling Rate	Up to 4800 SPS
Bandwidth (Hz)	Sampling Rate (SPS) / 4
Internal Resolution	24 bits
Resolution (Noise Free)	See Chart
Non-Linearity (max)	±0.005% of FSR
Input	Non-amplified (mV/V) Analog Voltage
Output	Digital Packetized Data
Integrated Digital Filter	50 Hz/60 Hz Rejection (100 dB)
On Chip Memory	1 Kilobyte
Stored Calibration	Up to 16 Points
Weight	approx. 10 g
STRAIN GAUGE mV/V INPUT	
Bridge Excitation	4.5 VDC
Standard Input Range	± 3.4 mV/V (factory default)
Optional Input Range	Up to \pm 400 mV/V
Min. Bridge Resistance	50 Ohm
Max. Bridge Resistance	5000 Ohm
CONNECTORS	
Sensor Connector	Hirose LX40-12P
Mating Connector	Hirose LX60-12S
USB 2.0 Connector	Type A Plug
ENVIRONMENT	
Operating Temperature	-13°F to 185°F [-25°C to 85°C]
Storage Temperature	-40°F to 257°F [-40°C to 125°C]
Temperature coefficient factor	10 ppm
CONFORMITY	
RoHS	2011/65/EU
CE	EN 61326-1:2006









りぐ


13485



U.S. Manufacturer

Model USB220

DIMENSIONS inches [mm]



LED INDICATORS	
Blinking blue (10 Hz)	Module Auto-Calibration
Blinking blue (1 Hz)	Module Normal Operation
Green	USB Power
Red	USB Data Link

RESOLUTION

ACCESSORIES

• FUTEK's SENSIT[™] Software (FSH03189)

14 Day Trial - Available to download on FUTEK website. A license is required, per seat, after 14 days to benefit the features such as data logging, graphing, etc. Trial version turns into basic read-out ONLY after 14 days and a product key is required to enable the features.

Drawing Number: FI1387

FUTEK reserves the right to modify its design and specifications without notice. Please visit <u>http://www.futek.com/salesterms</u> for complete terms and conditions.

10 Thomas, Irvine, CA 92618 USA Tel: (949) 465-0900 Fax: (949) 465-0905









13485



www.futek.com