




FEATURES

- Up to 10 times the overload protection
- Overload is available in Tension and Compression
- Light weight
- Notable nonlinearity
- Miniature size
- Ultra Low Capacity and High Sensitivity
- Vibration and shock resistance
- High flex silicone cable



SPECIFICATIONS			
PERFORMANCE			
Nonlinearity	±0.1% of RO		
Hysteresis	±0.1% of RO		
Nonrepeatability	±0.05% of RO		
ELECTRICAL			
Rated Output (RO)	See chart on third page		
Excitation (VDC or VAC)	10 max		
Bridge Resistance	1000 Ohm nom.		
Insulation Resistance	≥500 MOhm @ 50 VDC		
Connection	#29 AWG, 4 conductor, spiral shielded silicone cable, 5 ft [1.5 m] long		
Wiring Code	WC1		
MECHANICAL			
Weight (approximate)	0.7 oz [19.3 g] (10–250 g)		
Safe Overload	1000% of RO		
Material	Aluminum (10–250 g)		
IP Rating	IP40		
Vibration Resistance	20-2000 Hz, 0.01g²/Hz per MIL-STD-810E		
Shock Resistance	500 g per IEC60068-2-27		
TEMPERATURE			
Operating Temperature	-60 to 200°F [-50 to 93°C]		
Compensated Temperature	60 to 160°F [15 to 72°C]		
Temperature Shift Zero	±0.01% of RO/°F [0.018% of RO/°C]		
Temperature Shift Span	±0.02% of Load/°F [0.036% of Load/°C]		
CALIBRATION			
Calibration Test Excitation	5 VDC		
Calibration (standard)	5-pt Tension		
Calibration (available)	5-pt Tension and Compression		
Shunt Calibration Value	301 kOhm (10–20 g) 150 kOhm (50–250 g)		
CONFORMITY			
RoHS	EU 2015/863		
CE	EN55011; EN61326-1		


















Model LSB200


DIMENSIONS inches [mm]

TOLERANCE: X ± 0.1" [2.5 mm] .XX ± 0.005" [0.127 mm] 2X M3x0.5 - 6H I 0.11 0.092 [2.34] 0.092 [2.34] 0.185 [4.70] 0.315 [8.00] 0.092 [2.34] 0.185 [4.70]

WIRING CODE (WC1)				
RED	+ EXCITATION			
BLACK	– EXCITATION			
GREEN	+ SIGNAL			
WHITE	– SIGNAL			
SHIELD	FLOATING			



CAPACITIES						
ITEM #	g	N	RO (nom)	Deflection	Natural Frequency (Hz)	
FSH03867	10 g	0.1	0.5 mV/V	0.004 in [0.10 mm]	140	
FSH03868	20 g	0.2	1 mV/V	0.008 in [0.20 mm]	140	
FSH03869	50 g	0.5		0.010 in [0.25 mm]	200	
FSH03870	100 g	1.0	2 mV/V	0.008 in [0.20 mm]	300	
FSH03871	250 g	2.5		0.007 in [0.18 mm]	530	



Drawing Number: FI1455-B

FUTEK reserves the right to modify its design and specifications without notice. Please visit www.futek.com/salesterms for complete terms and conditions.













