

Terms and Conditions of Use

This drawing, including all information depicted herein (collectively, "Drawing"), is FUTEK's property and protected under applicable law, including copyright. FUTEK reserves all rights. The Drawing is provided solely for your information and exclusive use. **Except as expressly approved by FUTEK in writing, you may not reproduce or share this Drawing**, in whole or part, with any other firm or individual, or attempt to reverse engineer the Drawing or data contained therein. Any reproduction of this Drawing in whole or part must include this legend.

By accessing the Drawing, you agree that you have read, understand, and agree to abide by the stated Terms and Conditions of Use.

© 2023 FUTEK Advanced Sensor Technology, Inc.




FUTEK MODEL QLA374

ITEM NUMBER: QSH01670

CUSTOM LOW PROFILE COMPRESSION PANCAKE LOAD CELL

-OUTPUT
(COMPRESSION)

INCH [mm]		R.O.= Rated Output	
WIRING CODE (CC1)			
+ Excitation	- Excitation	+ Signal	- Signal
PIN A	PIN B	PIN C	PIN D
+ Sense	-Sense		
PIN E	PIN F		



SPECIFICATIONS:

RATED OUTPUT	4 mV/V nom.
CAPACITY	50000 lb [222kN]
SAFE OVERLOAD	150% of R.O.
ZERO BALANCE	±3% of R.O.
EXCITATION (VDC OR VAC)	20 MAX
BRIDGE RESISTANCE	350 Ω nom
NONLINEARITY	±0.2% of R.O.
HYSTERESIS	±0.2% of R.O.
NONREPEATABILITY	±0.05% of R.O.
TEMP. SHIFT ZERO	±0.01% of R.O./°F [±0.0018% of R.O./°C]
TEMP. SHIFT SPAN	±0.005% of LOAD/°F [±0.0036% of LOAD/°C]
COMPENSATED TEMP.	60 to 160 °F (15 to 71 °C)
OPERATING TEMP	-60 to 200 °F (-51 to 93 °C)
WEIGHT (approx)	10 lb [4.5 kg]
MATERIAL	17-4ph S.S.
CONNECTOR:	6 Pin AMPHENOL MS3102E14s-6p

CUSTOMER APPROVAL- COMPANY:

CUSTOMER APPROVAL- NAME / DATE:

REVISIONS: (Refer to dwg # revision sheet)

OUTLINE DRAWING


STANDARD NOTES: (Unless Otherwise Specified)

ALL DIMENSIONS ARE IN INCHES
DRAWING INTERPRETATION DIMS. PER ASME-Y14.5M
REMOVE BURRS AND BREAK SHARP EDGES .005 - .015
THREADS PER HANDBOOK H-28
DIMENSIONS ARE SHOWN AFTER PLATING

ANGLE:
± 1/2

CHAMFER:
± 5

TOLERANCE:
.X ± 0.1"
.XX ± 0.01"
.XXX ± 0.005"



FUTEK

This drawing, including all information depicted herein (collectively, "Drawing"), is FUTEK's property and protected under applicable law, including copyright. FUTEK reserves all rights. The Drawing is provided solely for your information and exclusive use. Except as expressly approved by FUTEK in writing, you may not reproduce or share this Drawing in whole or part, with any other firm or individual, or attempt to reverse engineer the Drawing or data contained therein. Any reproduction of this Drawing in whole or part must include this legend.

MODEL: QLA374	DWG No.: FO1350
DRAWN BY: M. Lisiak	CREATED DATE: 5/20/2015
APPROVED BY: R. Walker	APPROVED DATE: 5/22/2015
CHECKED BY:	CAGE: 1X8M6 SHEET: 1 OF 1