




**FEATURES**

- High accuracy
- Overload protection
- For use in both tension and compression
- Integrated connector, detachable cable available

**Active end**



**Fixed end**

**SPECIFICATIONS**

**PERFORMANCE**

Nonlinearity	±0.05% of RO
Hysteresis	±0.05% of RO
Nonrepeatability	±0.05% of RO
Creep	±0.05% of Load

**ELECTRICAL**

Rated Output (RO)	2 mV/V nom
Excitation (VDC or VAC)	18 max
Bridge Resistance	1000 Ohm nom
Insulation Resistance	≥500 Mohm @ 50 VDC
Connection	4 Pin LEMO Receptacle
Connector Code	CC4

**MECHANICAL**

Weight (approximate)	5 oz [140 g]
Safe Overload	See chart on next page
Material	Aluminum, Red Anodized (Housing)
IP Rating	IP40

**TEMPERATURE**

Operating Temperature	-60 to 200°F [-50 to 93°C]
Compensated Temperature	60 to 160°F [15 to 71°C]
Temperature Shift Zero	±0.005% of RO/°F [0.01% of RO/°C]
Temperature Shift Span	±0.005% of Load/°F [0.01% of Load/°C]

**CALIBRATION**

Calibration Test Excitation	10 VDC
Calibration (standard)	5-pt compression
Calibration (available)	Tension and Compression
Shunt Calibration Value	150 kOhm

**Sensor Solution Source**


Load · Torque · Pressure · Multi-Axis · Calibration · Instruments · Software

[www.futek.com](http://www.futek.com)



U.S. Manufacturer

**DIMENSIONS** inches [mm]




**CAPACITIES**

ITEM #	lb	N	Safe Overload (lb)	Deflection (in)	Natural Frequency (Hz)
FSH00259	0.25	1.1	50	0.0024	220
FSH00260	0.50	2.2	50	0.0014	390
FSH00261	1	4.5	50	0.0043	320
FSH00262	2.2	9.8	250	0.0040	320
FSH00263	5	22.2	250	0.0049	430
FSH00264	10	44.5	250	0.0046	630
FSH00265	25	111	250	0.0046	990
FSH00266	50	222	250	0.0044	1430
FSH00267	100	445	250	0.0048	1930

**LEMO 4-PIN (CC4)**

PIN	COLOR	DESCRIPTION
1	Red	+ Excitation
2	Green	+ Signal
3	White	- Signal
4	Black	- Excitation



Drawing Number: FI1040-E

FUTEK reserves the right to modify its design and specifications without notice. Please visit [www.futek.com/salesterms](http://www.futek.com/salesterms) for complete terms and conditions.

10 Thomas, Irvine, CA 92618 USA

Tel: (949) 465-0900

Fax: (949) 465-0905

[www.futek.com](http://www.futek.com)



U.S. Manufacturer