

## Terms and Conditions of Use

This drawing, including all information depicted herein (collectively, "Drawing"), is FUTEK's property and protected under applicable law, including copyright. FUTEK reserves all rights. The Drawing is provided solely for your information and exclusive use. **Except as expressly approved by FUTEK in writing, you may not reproduce or share this Drawing**, in whole or part, with any other firm or individual, or attempt to reverse engineer the Drawing or data contained therein. Any reproduction of this Drawing in whole or part must include this legend.

By accessing the Drawing, you agree that you have read, understand, and agree to abide by the stated Terms and Conditions of Use.

© 2023 FUTEK Advanced Sensor Technology, Inc.



# FUTEK MODEL LSM300 LEAD FREE LSM300 w/ FCI CONNECTOR

ITEM NUMBER: QSH01784



INCH (mm) | R.O. = Rated Output

WIRING CODE			
+Excitation	-Excitation	+Signal	-Signal
GREEN PIN '1'	BLACK PIN '4'	WHITE PIN '2'	RED PIN '3'
GROUND FLOATING PIN '5'			



## SPECIFICATIONS:

RATED OUTPUT	2 mV/V nom.
CAPACITY	5 lb
SAFE OVERLOAD	250 lb
ZERO BALANCE	±3% of R.O.
EXCITATION (VDC OR VAC)	18 MAX
BRIDGE RESISTANCE	1000 Ω nom.
NONLINEARITY	±0.02% of R.O.
HYSTERESIS	±0.02% of R.O.
NONREPEATABILITY	±0.02% of R.O.
CREEP	±0.025% of LOAD.
TEMP. SHIFT ZERO	±0.005% of R.O./°F [0.01% of R.O./°C]
TEMP. SHIFT SPAN	±0.005% of LOAD/°F [0.01% of LOAD/°C]
COMPENSATED TEMP.	60 to 160°F [15 to 72°C]
OPERATING TEMP.	-60 to 200°F [-50 to 93°C]
WEIGHT	1 oz [28 g]
MATERIAL	ALUMINUM
CABLE: #29 AWG, 4 Conductor, Spiral Shielded Silicone Cable	
RoHS LEAD FREE	YES
ISO13485 COMPLIANCE	YES
CE COMPLIANCE	EN55011:2009 EN 61326-1:2006

MATERIAL:	—
HEAT TREATMENT - FINISH:	—
REVISIONS: (Refer to dwg # revision sheet)	

## OUTLINE DRAWING

STANDARD NOTES: (Unless Otherwise Specified)

- ALL DIMENSIONS ARE IN INCHES
- DRAWING INTERPRETATION DIMS. PER ASME-Y14.5M
- REMOVE BURRS AND BREAK SHARP EDGES .005 - .015
- THREADS PER HANDBOOK H-28
- DIMENSIONS ARE SHOWN AFTER PLATING

ANGLE:

±1/2°

CHAMFER:

±5°

TOLERANCE:

.X ±0.1

.XX ±0.01

.XXX ±0.005

3rd ANGLE PROJ.



# FUTEK

This drawing, including all information depicted herein (collectively, "Drawing"), is FUTEK's property and protected under applicable law, including copyright. FUTEK reserves all rights. The Drawing is provided solely for your information and exclusive use. Except as expressly approved by FUTEK in writing, you may not reproduce or share this Drawing, in whole or part, with any other firm or individual, or attempt to reverse engineer the Drawing or data contained therein. Any reproduction of this Drawing in whole or part must include this legend.

CAGE: 1X8M6

MODEL: LSM300

DWG No. FO1386

DRAWN BY: E. Pano

CHECKED BY: -

APPROVED BY: R. Walker

DATE: Feb, 26 2015