

## Terms and Conditions of Use

This drawing, including all information depicted herein (collectively, "Drawing"), is FUTEK's property and protected under applicable law, including copyright. FUTEK reserves all rights. The Drawing is provided solely for your information and exclusive use. **Except as expressly approved by FUTEK in writing, you may not reproduce or share this Drawing**, in whole or part, with any other firm or individual, or attempt to reverse engineer the Drawing or data contained therein. Any reproduction of this Drawing in whole or part must include this legend.

By accessing the Drawing, you agree that you have read, understand, and agree to abide by the stated Terms and Conditions of Use.


© 2023 FUTEK Advanced Sensor Technology, Inc.

# FUTEK MODEL QLA383

ITEM NUMBER: TPS01031

## LOW PROFILE CALIBRATION TRIPOD WITH IAA100 VOLTAGE AMPLIFIER MODULES

INCH [mm] | R.O.= Rated Output



### SPECIFICATIONS:

RATED OUTPUT	10 VDC @333.33 g (each channel calibrated simultaneously)
POWER SUPPLY	12.5 - 26 VDC
CAPACITY	1000 g
MAX LOAD	2000 g
WEIGHT (approx)	90 g
MATERIAL	Aluminum
CABLE	3x 29 AWG Spiral Shielded Silicone, 5 ft [1.5 m] long

SEE IAA100 SPECIFICATIONS FOR FURTHER ELECTRONIC DETAILS.

CUSTOMER APPROVAL- COMPANY:	<h1 style="color: green;">OUTLINE DRAWING</h1>			
CUSTOMER APPROVAL- NAME / DATE:			<p>STANDARD NOTES: (Unless Otherwise Specified)</p> <p>ALL DIMENSIONS ARE IN INCHES</p> <p>DRAWING INTERPRETATION DIMS. PER ASME-Y14.5M</p> <p>REMOVE BURRS AND BREAK SHARP EDGES .005 - .015</p> <p>THREADS PER HANDBOOK H-28</p> <p>DIMENSIONS ARE SHOWN AFTER PLATING</p>	<p><small>This drawing, including all information depicted herein (collectively, "Drawing"), is FUTEK's property and protected under applicable law, including copyright. FUTEK reserves all rights. The Drawing is provided solely for your information and exclusive use. Except as expressly approved by FUTEK in writing, you may not reproduce or alter this Drawing in whole or part with any other firm or individual, or attempt to reverse engineer the Drawing or data contained therein. Any reproduction of this Drawing in whole or part must include this legend.</small></p>
<p>REVISIONS: (Refer to dwg # revision sheet)</p> <table border="1" style="width: 100%; height: 20px;"> <tr> <td style="width: 50%;"></td> <td style="width: 50%;"></td> </tr> </table>			<p>ANGLE: ± 1/2°</p> <p>CHAMFER: ± 5°</p> <p>3rd ANGLE PROJ.</p> <p> </p> <p> <b>TOLERANCE:</b>                  .X ± 0.1"                  .XX ± 0.01"                  .XXX ± 0.005"             </p>	<p>MODEL: <b>QLA383</b> DWG No.: <b>FO1413</b></p> <p>DRAWN BY: M. Lisiak CREATED DATE: 12/16/2015</p> <p>APPROVED BY: R. Walker APPROVED DATE: 12/18/2015</p> <p>CHECKED BY: CAGE: 1X8M6 SHEET: 1 OF 1</p>